















Measuring spindles according to ASTM / ISO 2555 (316L stainless steel).
 These systems are ideally suited for simple viscosity measurement at controlled rotational speed in all areas of activity. The standard recommends use of 600ml beaker for measurement.
 These systems are compatible with all instruments and our temperature control EVA LR.

| Name | Part number | Dim. (mm) | |
|--|-------------|------------------|--|
| L-1 spindle | 111010 | Ø 18,80 - L 65,1 |  |
| L-2 spindle | 111011 | Ø 18,72 - L 6,86 |  |
| L-3 spindle | 111012 | Ø 12,60 - L 1,78 |  |
| L-4 spindle | 111013 | Ø 3,20 - L 31 |  |
| Axis R 1-6 without disc | 111000 | Threaded axis |  |
| R-1 Disc | 111001 | Ø 56,26 |       |
| R-2 Disc | 111002 | Ø 46,93 | |
| R-3 Disc | 111003 | Ø 34,69 | |
| R-4 Disc | 111004 | Ø 27,30 | |
| R-5 Disc | 111005 | Ø 21,14 | |
| R-6 Disc | 111006 | Ø 14,62 | |
| Axis R-7 | 111007 | Ø 3,20 |  |
| Axis L-R | 111008 | Adaptation axis |  |
| DELTRIN STAND L1 to L4 and/or R2 to R7 | 000590 | - |  |

SPINDLES WITH BAYONET COUPLING

| Designation spindle | Part Number Spindle | Part Number Complete set ^{b)} | Viscosity range for version LR (mPa.s) | Viscosity range for FIRST/B-ONE (mPa.s) | Viscosity range for RM100/200/DSR500 (mPa.s) | |
|---------------------|----------------------|--|--|---|--|-------------|
| RV1 | 111001 ^{a)} | 111947 | 111948 | Not Usable | 100 to 0.6M | 50 to 1.4M |
| RV2 | 111002 ^{a)} | | | 200 to 0.14M | 200 to 2.4M | 100 to 5.5M |
| RV3 | 111003 ^{a)} | | | 300 to 0.37M | 300 to 6M | 150 to 14M |
| RV4 | 111004 ^{a)} | | | 400 to 0.74M | 600 to 12M | 200 to 28M |
| RV5 | 111005 ^{a)} | | | 500 to 1.4M | 1.2K to 24M | 300 to 55M |
| RV6 | 111006 ^{a)} | | | 1200 to 3.7M | 2.8K to 60M | 500 to 130M |
| RV7 | 111007 | 111014 | | 4500 to 15M | 12K to 240M | 2K to 550M |
| LV1 | 111010 | | | 15 to 0.25M | 200 to 4.3M | 35 to 10M |
| LV2 | 111011 | | | 50 to 1.3M | 1K to 20M | 170 to 50M |
| LV3 | 111012 | | | 200 to 5M | 4k to 82M | 650 to 190M |
| LV4 | 111013 | | | 1000 to 22M | 17K to 370M | 3K to 860M |

M for millions, K for thousand a) Need additional axis (PN111000) b) Complete set (delivered with axis PN 111000 only for RV spindle)