

Test whatever you like.

From ABS units to a gear drive - in research, development and quality control, you won't want to take any chances. We'll support you.



From the North Pole to the Tropics.

Seasonal differences, different climatic zones - your products must be able to withstand a variety of temperatures during manufacturing, transport, storage and use. The Walk-in Chambers ClimeEvent help you to test the influence of temperature and humidity on the properties, function and lifespan of your products. Reproducible, certified and under accelerated conditions.

Simple and flexible.

Standardised solutions can be so flexible. Thanks to the modular system, the Walk-in Chambers ClimeEvent can be configured quickly and easily. The wide range of options enables us to meet your individual needs, resulting in a perfectly coordinated complete solution that will meet even the highest standards of your industry.

Perfection in performance, equipment and design.

Walk-in Chambers ClimeEvent.

Precisely engineered.

We know what matters for your tests: reliable, precise and reproducible results. That's why we design our test chambers to meet exactly these demands. Because incorrect results lead to incorrect conclusions. With your needs in mind, we already eliminate any interference factors during the design phase, relying on our comprehensive expertise and years of experience.




For us, quality is our daily business. We use only high-quality materials and manufacture many of the components for our test chambers in-house, primarily in the particularly challenging field of cooling technology. In addition, we have regular quality checks in place throughout the entire production process.

Absolutely low maintenance.

Set up, plug in, start the test. The intelligent, compatible control elements and intuitive user interface guarantee easy operation. Easily accessible maintenance elements ensure minimal service times. Diagnostics and inspection systems in every machine additionally shorten downtimes and optimise maintenance periods.





Highlights at a glance:

- New, eco-friendly refrigerant
- Highest level of control accuracy thanks to the perfect coordination of air conditioning, cooling technology and control units
- Web-based user interface WEBSeason®

 $\mathsf{2}$

More equipment, right from the start.

Basic equipment setting standards.



You can find further details on equipment in our technical descriptions. Contact us.

Exterior



• Move safely into the future - using the new refrigerant

The new refrigerant R449A is used in all Climate Test Chambers ClimeEvent. The GWP value of just 1397 ensures safe usage even after 2030, and the refrigerant does not have to be replaced. As a result, we are already surpassing the future statutory standards today, making your testing needs future-proof, the equipment easier to maintain and more environment-friendly.

• Efficient, more efficient, ClimeEvent

Thanks to numerous measures, e.g. a 200 mm thick double-layer insulation or latest generation high-efficiency EC fans, the Walk-in Chambers ClimeEvent are among the most efficient systems in their class. The electronic cooling water regulator installed in every system ensures a highly efficient operation, saving cost for operating water-cooled equipments.

Interior



• No chance for dirt or corrosion

The test chamber and the test chamber floor are made of highly-alloyed, extra corrosion-resistant stainless steel 1.4404, making the Walk-in Chamber ClimeEvent particularly durable.

Get involved

To insert individual measurement cables or supports into the chamber, two stainless steel ports with 125 mm diameter each are included as standard.

Regulation & Control



• Into the age of connectivity - with WEBSeason



You can use the innovative **WEB**Season user interface to program, control and monitor your tests at any time and anywhere, even from your tablet or smartphone. Language and units can be set to suit the user and the settings can be saved. In this way, **WEB**Season provides a new dimension of flexibility and efficiency.

Reliable control in series:

Digital measurement and control system for operating and monitoring of the test chamber.



 $oldsymbol{4}$

Tailor-made testing.

Optional equipment for individual solutions.

Exterior



• Great climate

With the optional climatic package expansion, climatic tests with climatic values between 10% and 95% RH at temperatures of +10 °C to +90 °C can be carried out in the compact chamber.

Everything in view

In addition to the multi-layered observation window in the door, up to six viewing windows can be installed in the side walls.

Interior



• Already available

You can simply add the PV 1200, PV 2005 and BMW 308.2 packages as they come in preconfigured standard options.

Regulation & Control



• Set standards in communication

With **S!M**PATI® software, operating, documenting and archiving your test sequences is very easy.



You can find further details on equipment in our technical descriptions. Contact us.



Developed exclusively for you: The unique software package for the perfect test process.



6

Advanced technology. Reliable results.

The performance data at a glance.

PERFORMANCES FOR	Exterior housing dimensions, HxWxD1	Test space dimensions, H×W×D	Test space volume	C Minimum temperature ²	Maximum Cemperature	X Temperature- changing rate, cooling³	M/M Changing rate, heating ³	Temperature N deviation in time ⁴	Temperature Nomogeneity in space ⁵	C Minimum temperature	المعنسس معنسات المعنسات المعاسات المعنسات المعنسات المعنسات المعنسات المعنسات المعنسات المعاسات المعنسات المعنسات المعنسات المعنسات المعنسات المعنسات المعا	Dewpoint temperature range ⁶	Humidity range	Humidity constancy in time ⁷	Temperature Nomogeneity in time ⁴	Temperature M homogeneity in space [§]
ClimeEvent T/9'/40/2 ClimeEvent T/9'/70/2	- 3480×3750×6710 2300×22 - 3180×3750×7710 2000×22	2000×2200×2100	9	-40 -70						celliane res	13					
ClimeEvent T/11'/40/2 ClimeEvent T/11'/70/2		2300×2200×2100	11	-40 -70 -40 -70 -40 +150												
ClimeEvent T/14'/40/2 ClimeEvent T/14'/70/2 ClimeEvent T/16'/40/2		2000×2200×3100	14		+150	2.0	2.0	±0.1 to ±0.5	±0.1 to ±2.0	Without climatic operation						
ClimeEvent T/16'/70/2 ClimeEvent T/18'/40/2	3480×3750×7710 3180×3750×8710	2300×2200×3100 2000×2200×4100	16 18	-70 -40												
ClimeEvent T/18'/70/2 ClimeEvent T/21'/40/2 ClimeEvent T/21'/70/2	3480×3750×8710	2300×2200×4100	21	-70 -40 -70												
ClimeEvent C/9'/40/2 ClimeEvent C/9'/70/2	3180×3750×6710	2000×2200×2100	9	-40 -70	-40		2.0	±0.1 to ±0.5	±0.1 to ±2.0	+10	+90	+6 to +88	10 to 95	±1 to ±5	±0.1 to ±0.5	±0.1 to ±2.0
ClimeEvent C/11'/40/2 ClimeEvent C/11'/70/2	3480×3750×6710 3180×3750×7710 3480×3750×7710 3180×3750×8710 3480×3750×8710	2300×2200×2100	11	-40 -70 -40 -70 -40												
ClimeEvent C/14'/40/2 ClimeEvent C/14'/70/2 ClimeEvent C/16'/40/2		2000×2200×3100	14		+150	2.0										
ClimeEvent C/16'/70/2 ClimeEvent C/18'/40/2		2300x2200x3100	16 18 21	-70 -40												
ClimeEvent C/18'/70/2 ClimeEvent C/21'/40/2		2000×2200×4100 2300×2200×4100		-70 -40												
ClimeEvent C/21'/70/2 Calibration values:	740077,000110	-70 +23 °C and +80 °C for all models								+23 °C/50% RH and +90 °C/50% RH for all ClimeEvent C						

The performance data refer to +25 $^{\circ}\text{C}$ ambient temperature and +27 $^{\circ}\text{C}$ cooling water temperature, 400 V/50 Hz nominal voltage, without specimen, without optional equipment and without heat compensation. The product needs fluorinated gases for functioning. Depending on the type, it contains refrigerants R449A and R23. We reserve the right to make any technical changes without prior notice.

Including aggregation unit and maintenance area. The required clearances can be reduced by dismounting components.

Temperatures >+5 °C are permitted in continuous operation; temperatures <+5 °C are permitted discontinuously or with the addition of a compressed air dryer.

³According to IEC 60068-3-5; average, measured in the supply air.

In the middle of the test space when it is empty and in steady state, without specimen, without heat radiation and without additional equipment, depending on temperature. Relative to the selected set point in the temperature range from the minimum temperature up to $+150\,^{\circ}\text{C}$ or with humidity $>20\,\%$ RH.

 $^{^{6}}$ Discontinuous operation (+4 $^{\circ}$ C to -3 $^{\circ}$ C). 7 In the middle of the test space when it is empty and in steady state, depending on climatic value.

Become more efficient.

Our solutions will save you time and money.

Get the most out of your test facility.



Create your own perfect testing process with the S!MPATI® software package.

Process management/documentation/networking

- Up to 99 systems can be connected
- Programs for automated processes
- Documentation, visualisation and management of process data
- Traceability of process data for seamless quality control



We measure ourselves by our service!

Our services - lots of good reasons:

- Global service network
- Wide selection of preventive maintenance
- Reliable spare part supply
- Special deployments available any time
- Certified proper disposal of outdated devices

You can always find a **weiss**technik expert near you.

Quicker, longer, harder.

Test Chambers for special requirements.

You want to test a large item and need a test chamber with a greater interior volume? Or you need faster heat-up and/or cool-down rates? No problem! As required, we can provide you with special solutions that are tailored exactly to your requirements. Get in touch with us!

10 11

24/7-Service-Helpline:

+49 1805 666 556

Passionately innovative.

We work in partnership to support companies in research, development, production and quality assurance. With 22 companies in 15 countries at 40 locations.

weisstechnik
Test it. Heat it. Cool it.



Environmental Simulation

The first choice for engineers and researchers for innovative, safe environmental simulation facilities. In fast motion, our test systems can simulate all the influences in the world as well as for instance in space. In temperature, climate, corrosion, dust or combined stress tests. With a very high degree of reproducibility and precision.



Heat Technology

Experienced engineers and designers develop, plan and produce high-quality, reliable heat technology systems for a broad range of applications from heating and drying cabinets to microwave systems and industrial furnaces.





Climate Technology, Air Dehumidification, Clean Rooms

As the leading provider of clean rooms, climate technology and air dehumidification, we consistently ensure optimal climatic conditions for people and machines. For industrial production processes, in hospitals, mobile operation tents or in the field of information and telecommunications technology. From project planning to implementation.



Clean Air and Containment Systems

With decades of experience and know-how, we guarantee the most sophisticated clean air and containment solutions. Our comprehensive and innovative range of products includes barrier systems, laminar flow systems, safety workbenches, isolators and airlocks.





UT-ClimeEvent-WalkIn-01.2E/PP 1.0/04 2018

Weiss Umwelttechnik GmbH

Greizer Straße 41-49 35447 Reiskirchen/Germany T +49 6408 84-0 info@weiss-technik.com www.weiss-technik.com



